



Straight Blade Devices, Male Inlets, Flanged, Industrial/Commercial, Nylon Cup, 15A 250V, 2-Pole 3-Wire Grounding, 6-15P, White, Single Pack

By Bryant
Catalog # 5678



Straight Blade Devices, Male Inlets, Flanged, Industrial/Commercial, Nylon Cup, 15A 250V, 2-Pole 3-Wire Grounding, 6-15P, White, Single Pack

Features

- Flanged
- Industrial/Commercial
- Nylon Cup
- 15A 250V
- 2-Pole 3-Wire Grounding

Application

Extra Heavy Duty Industrial

General

Catalog Number	5678
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Single Flanged
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Heavy Duty
Style	Clamp Type
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786626041

Dimensions

Dimensions	1.84 in x 2.50 in x 1.55 in
Display Size	Standard Sized Product

Height	1.55 in
Length	1.84 in
Weight	0.05 lb
Width	2.5 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	3750

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance

Nema Rating	6-15P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 5678 Specification Sheet English](#)
- [Specifications - 5678 Specification Sheet French](#)