



Straight Blade Devices, Female Receptacles, Flanged, Industrial Grade, 15A 250V, 2-Pole 3-Wire Grounding, 6-15P, White, Single Pack

By Bryant
Catalog # 5679

Straight Blade Devices, Female Receptacles, Flanged, Industrial Grade, 15A 250V, 2-Pole 3-Wire Grounding, 6-15P, White, Single Pack

Features

- Flanged
- Industrial Grade
- 15A 250V
- 2-Pole 3-Wire Grounding
- 6-15P

Application

Commercial/Industrial

Specifications

Standards - RoHS Compliance	CM
Status	
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Nema Rating	6-15R

Conductor

Number Of Wires	3-Wire
Number Of Poles	2-Pole

Current



Amperage Rating	15 A
Voltage Rating Description	250 V
Voltage Rating	250 V
Current / Amperage Rating	15 A

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

Color	White
Series	Heavy Duty
OEM Brand Name	Hubbell Bryant
UPC	781786663909
Type	Flanged Receptacle
Item Type	Smooth Face

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)