



Straight Blade Devices, Receptacles, Panel Mount Single, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Brown, Single Pack

By Bryant
Catalog # 5684

Straight Blade Devices, Receptacles, Panel Mount Single, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Brown, Single Pack

Features

- Panel Mount Single
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- 15A 250V
- 6-15R

Specifications

Environmental Conditions Indoor Dry Unless Protected By Additional Means

Nema Rating 6-15R

Conductor

Number Of Wires 3-Wire
Number Of Poles 2-Pole

Current

Current Rating 15 A
Amperage Rating 15 A
Voltage Rating Description 250 V
Phase Single Phase
Current / Amperage Rating 15 A
Wattage 5000 W
Voltage Rating 250 V



Dimensions

Display Size Standard Sized Product
Length 1.94 in
Width 1.38 in
Weight 0.05 lb.
Height 0.81 in
Dimensions 1.94 in x 1.38 in x 0.81 in

General

Series Extra Heavy Duty
OEM Brand Name Hubbell Bryant
Style Finder Groove Face
Color Brown
Material - Mounting Hardware Screw Mounting
Type Specialty Receptacle
UPC 781786626072

Logistics

Carton Quantity 10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)