



Straight Blade Devices, Female Connector, Valise Series, Commercial Grade, Straight, 2-Pole 3-Wire Grounding, Insulation Displacement, 15A 125V, 5-15R

By Bryant
Catalog # 5969VBK

Straight Blade Devices, Female Connector, Valise Series, Commercial Grade, Straight, 2-Pole 3-Wire Grounding, Insulation Displacement, 15A 125V, 5-15R, Black, Single Pack

Features

- Valise Series
- Commercial Grade
- Straight
- 2-Pole 3-Wire Grounding
- Insulation Displacement

Application

Heavy Duty

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire
Number Of Conductors	3-Wire Grounding
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Insulation Displacement
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Length	2.25 in
Width	1.25 in
Weight	0.05 lb.
Height	1.17 in
Dimensions	2.25 in x 1.25 in x 1.17 in

General

Series	Commercial
OEM Brand Name	Hubbell Bryant
Style	Heavy Duty
Color	Black
Item Type	Valise
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	781786626607

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	- Maximum Continuous: 75° C - Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)

