



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Manual Motor Controllers, Three Pole, 60A 600V AC, Side Wired Only, Black

By Bryant
Catalog # 60003D

Switches and Lighting Controls, Industrial Grade, Toggle Switches, Manual Motor Controllers, Three Pole, 60A 600V AC, Side Wired Only, Black



Features

- Toggle
- Manual Motor Controllers
- Three Pole
- 60A 600V AC
- Side Wired Only

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM

Conductor

Number Of Poles	3 Pole
-----------------	--------

Current

Current Rating	60 A
Amperage Rating	60 A
Voltage Rating Description	600V AC kV
Phase	Three Phase
Current / Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Wattage	36000
Voltage Rating	600V AC kV

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Force Related

Load Capacity	Inductive
---------------	-----------

General

Series	Standard Toggle
Style	Motor Controller/Disconnect
Item Type	Open Switch
Material - Mounting Hardware	Screw Mounting
Type	Back Wire
UPC	781786631748

Logistics

Carton Quantity	10
Pallet Quantity	1170

Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact

Product Assets

[Catalog \[English\]](#)