



# Industrial Grade, Toggle Switches, Manual Motor Controllers, Double Pole, 60A 600V AC, Side Wired Only, With NEMA 3R Enclosure

By Bryant  
Catalog # 60302D

Switches and Lighting Controls, Industrial Grade, Toggle Switches, Manual Motor Controllers, Double Pole, 60A 600V AC, Side Wired Only, Black, With NEMA 3R Enclosure



## Features

- Toggle
- Manual Motor Controllers
- Double Pole
- 60A 600V AC
- Side Wired Only

## Application

Red Slide

## Specifications

Environmental Conditions	Indoor and Outdoor
EU RoHS Indicator	No
Standards - RoHS Compliance Status	CM

## Conductor

Number Of Poles	2 Pole
-----------------	--------

## Current

Current Rating	60 A
Amperage Rating	60 A
Voltage Rating Description	600V AC kV
Phase	Single Phase
Current / Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Wattage	36000
Voltage Rating	600V AC kV

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Force Related

Load Capacity	Inductive
---------------	-----------

## General

Enclosure Type	NEMA 3R
Series	Non-Fused
OEM Brand Name	Hubbell Bryant
Style	Standard Duty
Item Type	Enclosed Switch
Material - Mounting Hardware	Screw Mounting
Type	Disconnect Switches
UPC	781786631779

## Logistics

Carton Quantity	4
-----------------	---

## Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact

## Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)