



Industrial Grade, Toggle Switches, Manual Motor Controllers, Three Pole, 60A 600V AC, Side Wired Only, With NEMA 3R Enclosure

By Bryant
Catalog # 60303D



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Manual Motor Controllers, Three Pole, 60A 600V AC, Side Wired Only, Black, With NEMA 3R Enclosure

Features

- Toggle
- Manual Motor Controllers
- Three Pole
- 60A 600V AC
- Side Wired Only

Application

Red Slide

General

Catalog Number	60303D
EU RoHS Indicator	No
Enclosure Type	NEMA 3R
Environmental Conditions	Indoor and Outdoor
Item Type	Enclosed Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3 Pole
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Non-Fused
Style	Standard Duty
Type	Disconnect Switches
UPC	781786631786

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Three Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	36000

Certifications And Compliance

Standards - RoHS Compliance CM Status

Logistics

Carton Quantity 4

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 60303D Specification Sheet French](#)
[Specifications - 60303D Specification Sheet English](#)