



# Locking Devices, Marine Grade, Female Connector Body, 20A 125V, 2-Pole 3-Wire Grounding, L5-20R, Screw Terminal, Yellow, Corrosion Resistant

By Bryant  
Catalog # 70520NCCR



Locking Devices, Marine Grade, Female Connector Body, 20A 125V, 2-Pole 3-Wire Grounding, L5-20R, Screw Terminal, Yellow, Corrosion Resistant

## Features

- Nickel-plated copper-alloy metallic components
- Molded of impact/chemical resistant high-visibility yellow nylon
- Stainless steel screws
- Receptacles have a one-piece grounding system with built-in self-grounding strap
- Triple Gripper® cord grip on plugs and connectors which feature three captive assembly screws to automatically tighten cord grip
- Individual wire pockets with clamp-type terminals

## Application

Heavy Duty Industrial

## Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L5-20R

## Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Conductors	3-Wire Grounding
Conductor Range	#14 AWG to #12 AWG
Number Of Poles	2-pole

## Current

Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A

Voltage Rating Description	125 V
Connectivity	Screw Terminals
Voltage Rating	125 V

## Dimensions

Display Size	Standard Sized Product
Length	2.13 in
Height	3.90 in

## General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Yellow, White
Item Type	20A Triple Gripper Nylon Connector
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted Connector Body
Type	
Material	Composite
UPC	781786688605

## Logistics

Carton Quantity	10
-----------------	----

## Operational

Temperature Rating	<ul style="list-style-type: none"> <li>• Maximum Continuous: 75° C</li> <li>• Minimum Continuous: -40° C w/o impact, -25° with impact.</li> </ul>
--------------------	---

## Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)