



Locking Devices, Industrial, Male Plug, 20A 125V, 2-Pole3-Wire Grounding, L5-20P, Screw Terminal, Black and White

By Bryant
Catalog # 70520NP

Locking Devices, Industrial, Male Plug, 20A 125V, 2-Pole3-Wire Grounding, L5-20P, Screw Terminal, Black and White

Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions Indoor Dry Unless Protected By Additional Means

EU RoHS Indicator Yes

Standards - RoHS Compliance CM

Status

Nema Rating L5-20P

Conductor

Number Of Wires 3-Wire

Wire Size #18 AWG to #8 AWG

Number Of Poles 2-Pole

Configuration

Cord Type All Listed Portables

Current



Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125 V
Phase	Single Phase
Connectivity	Screw Terminals
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized
Length	2.13 in
Width	2.13 in
Height	2.86 in
Dimensions	2.13 in x 2.13 in x 2.86 in

General

Style	Internal Cord Clamp
Color	Black, White
Item Type	20A Triple Gripper Nylon Plug
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786688629

Logistics

Carton Quantity	10
Pallet Quantity	1680

Product Assets

[Catalog \[English\]](#)