



Locking Devices, Industrial, Female Connector Body, 30A 125V, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, Black

By Bryant
Catalog # 70530NCB

Locking Devices, Industrial, Female Connector Body, 30A 125V, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, Black

Features

- Face and body feature alignment keys for easy assembly
- Amperage, voltage and NEMA configuration imprinted on face for easy identification
- Impact/chemical resistant, toughened nylon construction
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L5-30R

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Conductors	3-Wire Grounding
Conductor Range	#12 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating	30 Amp
Description	
Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	125 V
Connectivity	Screw Terminals
Voltage Rating	125 V



Dimensions

Display Size	Standard Sized Product
Length	2.13 in
Width	2.13 in
Height	3.90 in
Dimensions	2.13 in x 2.13 in x 3.90 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	All Black
Item Type	30A Triple Gripper Nylon Connector
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	781786666597

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)