



Locking Devices, Isolated Ground
Industrial, Duplex Receptacle, 15A 250V, 2-
Pole 3-Wire Grounding, L6-15R, Screw
Terminal, Orange

By Bryant
Catalog # 70615DRIG

Locking Devices, Isolated Ground Industrial, Duplex Receptacle,
15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal,
Orange

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- Single point break-off tabs
- Mounting strap tabs lock the body and base together

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	L6-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating	15 Amp
Description	
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	250V



Phase	Single Phase
Connectivity	Terminal Screws
Voltage Rating	250 V

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.70 in
Height	1.17 in
Dimensions	3.28 in x 1.70 in x 1.17 in

General

Series	Locking
OEM Brand Name	Hubbell Bryant
Style	Isolated Ground
Item Type	15A Duplex Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Duplex Receptacle
Material	Composite
UPC	781786616318

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)