



Locking Devices, Industrial, Flanged Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, White

By Bryant
Catalog # 70615ER

Locking Devices, Industrial, Flanged Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, White

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	L6-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating Description	15 Amp
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	250V



Phase	Single Phase
Connectivity	Terminal Screws
Voltage Rating	250 V

Dimensions

Display Size	Standard Sized Product
Length	1.84 in
Width	2.50 in
Height	1.68 in
Dimensions	1.84 in x 2.50 in x 1.68 in

General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	White
Item Type	15A Flanged Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Flanged Receptacle
Material	Composite
UPC	781786703957

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)