



Locking Devices, Industrial, Male Plug, 20A 250V, 2-Pole3-Wire Grounding, L6-20P, Screw Terminal, Black and White

By Bryant
Catalog # 70620NP

Locking Devices, Industrial, Male Plug, 20A 250V, 2-Pole3-Wire Grounding, L6-20P, Screw Terminal, Black and White

Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	L6-20P

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	2-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current

Current/Amperage Rating	20 Amp
Description	



Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	250 V
Phase	Single Phase
Connectivity	Screw Terminals
Voltage Rating	250 V

Dimensions

Display Size	Standard Sized
Length	2.13 in
Width	2.13 in
Height	2.86 in
Dimensions	2.13 in x 2.13 in x 2.86 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Black, White
Item Type	20A Triple Gripper Nylon Plug
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786689329

Logistics

Carton Quantity	10
Pallet Quantity	1920

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)