



Locking Devices, Industrial, Flush Receptacle, 20A 480V AC, 2-Pole 3-Wire Grounding, L8-20R, Screw Terminal, Black

By Bryant
Catalog # [70820FR](#)



Locking Devices, Industrial, Flush Nylon Receptacle, 20A 480V AC, 2-Pole 3-Wire Grounding, L8-20R, Screw Terminal, Black/White

Features

- Combination back and side wiring terminals accept #14 through #8 AWG solid or stranded conductors
- Heavy duty mounting straps are nickel-plated to resist corrosion, wide width design assures secure assembly
- NEMA rating and configuration are molded into face for easy identification
- One-piece, rivetless copper-alloy contact design reduces heat buildup and provides secure blade retention

Application

Extra Heavy Duty Industrial Specification Grade

General

| | |
|------------------------------|---|
| Catalog Number | 70820FR |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | 20A Single Nylon Receptacle |
| Material | Composite |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| Style | Single Receptacle |
| Type | Receptacle |
| UPC | 781786690837 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 3.28 in x 1.70 in x 1.24 in |
| Display Size | Standard Sized Product |

| | |
|--------|---------|
| Height | 1.24 in |
| Length | 3.28 in |
| Width | 1.7 in |

Electrical Ratings

| | |
|----------------------------|-----------------|
| Amperage Rating | 20 A |
| Connectivity | Terminal Screws |
| Current Rating | 20 A |
| Phase | Single Phase |
| Voltage Rating | 480 VAC |
| Voltage Rating Description | 480V AC |

Conductor Related

| | |
|-----------------|-------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #14 AWG to #8 AWG |

Certifications And Compliance

| | |
|------------------------------------|--------|
| Nema Rating | L8-20R |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 70820FR Specification Sheet French](#)
- [Specifications - 70820FR Specification Sheet English](#)