



Locking Devices, Industrial, Female Connector Body, 20A 480V AC, 2-Pole 3-Wire Grounding, L8-20R, Screw Terminal, Black and White

By Bryant
Catalog # [70820NC](#)

Locking Devices, Industrial, Female Connector Body, 20A 480V AC, 2-Pole 3-Wire Grounding, L8-20R, Screw Terminal, Black and White

Features

- Face and body feature alignment keys for easy assembly
- Amperage, voltage and NEMA configuration imprinted on face for easy identification
- Impact/chemical resistant, toughened nylon construction
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance	CM
Status	
Nema Rating	L8-20R

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Conductors	3-Wire Grounding
Conductor Range	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A



Voltage Rating Description	480 VAC
Connectivity	Screw Terminals
Voltage Rating	480 VAC

Dimensions

Display Size	Standard Sized Product
Length	2.13 in
Height	3.90 in

General

Style	Internal Cord Clamp
Color	Black, White
Item Type	20A Triple Gripper Nylon Connector
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted Connector Body
Type	Connector Body
Material	Composite
UPC	781786690899

Logistics

Carton Quantity	10
Pallet Quantity	2080

Operational

Temperature Rating	<ul style="list-style-type: none">• Maximum Continuous: 75° C• Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)