



Locking Devices, Industrial, Female
Connector Body, 20A 250V, 2-Pole 2-Wire
Non-Grounding, L2-20R, Screw Terminal,
Gray

By Bryant
Catalog # 7102N

Locking Devices, Industrial, Female Connector Body, 20A 250V,
2-Pole 2-Wire Non-Grounding, L2-20R, Screw Terminal, Gray

Features

- Plug
- 20A 250V
- 2-Pole 2-Wire Non-Grounding
- L2-20
- Screw Terminal

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L2-20P

Conductor

Number Of Wires	2-Wire
Number Of Conductors	2-Pole Non-Grounding
Conductor Range	#14 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	250 V
Connectivity	Screw Terminals
Voltage Rating	250 V



Dimensions

Display Size	Standard Sized Product
Length	1.53 in
Width	1.53 in
Height	1.97 in
Dimensions	1.53 in x 1.53 in x 1.97 in

General

OEM Brand Name	Hubbell Bryant
Style	Two-Piece Cord Clamp
Color	Black, White
Item Type	20A Plug
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786715509

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)