



## Locking Devices, Industrial, Flanged Receptacle, 30A 3-Phase Delta 250V AC, 3-Pole 3-Wire Non Grounding, L11-30R, Screw Terminal, White

By Bryant  
Catalog # [71130ER](#)

Locking Devices, Industrial, Flanged Receptacle, 30A 3-Phase Delta 250V AC, 3-Pole 3-Wire Non Grounding, L11-30R, Screw Terminal, White



### Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

### Application

Extra Heavy Duty Industrial Specification Grade

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	L11-30R

### Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	3-Pole

### Current

Current/Amperage Rating	30 Amp
Description	
Current Rating	30 A
Amperage Rating	30 A

Voltage Rating Description	3 Phase 250V AC
Phase	Three Phase
Connectivity	Terminal Screws
Voltage Rating	3 Phase 250 VAC

### Dimensions

Display Size	Standard Sized Product
Length	2.88 in
Width	2.88 in
Height	2.02 in
Dimensions	2.88 in x 2.88 in x 2.02 in

### General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	White
Item Type	30A Flanged Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Flanged Receptacle
Material	Composite
UPC	781786693708

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)