



Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase Delta 250V AC, 3-Pole 3-Wire Non-Grounding, L11-30R, Screw Terminal, Black



By Bryant
Catalog # 71130FR

Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase Delta 250V AC, 3-Pole 3-Wire Non-Grounding, L11-30R, Screw Terminal, Black

Features

-
-
-
-

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	71130FR
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Style	Single Receptacle
Type	Receptacle
UPC	781786693739

Dimensions

Dimensions	3.28 in x 1.70 in x 1.24 in
Display Size	Standard Sized Product
Height	1.24 in
Length	3.28 in

Width 1.7 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Three Phase
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250V AC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L11-30R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 71130FR Specification Sheet French](#)
[Specifications - 71130FR Specification Sheet English](#)