



Locking Devices, Industrial, Female
Connector Body, 30A 3-Phase Delta 480V
AC, 3-Pole 3-Wire Non-Grounding, L12-
30R, Screw Terminal, Black and White

By Bryant
Catalog # 71230NC



Locking Devices, Industrial, Female Connector Body, 30A 3-
Phase Delta 480V AC, 3-Pole 3-Wire Non-Grounding, L12-30R,
Screw Terminal, Black and White

Features

- Face and body feature alignment keys for easy assembly
- Amperage, voltage and NEMA configuration imprinted on face for easy identification
- Impact/chemical resistant, toughened nylon construction
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	L12-30R

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Conductors	3-Wire Non-Grounding
Conductor Range	#12 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	30 Amp
Description	
Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	3 Phase 480 VAC
Connectivity	Screw Terminals

Voltage Rating	3 Phase 480 VAC
Dimensions	
Display Size	Standard Sized Product
Length	2.13 in
Width	2.13 in
Height	3.90 in
Dimensions	2.13 in x 2.13 in x 3.90 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Black, White
Item Type	30A Triple Gripper Nylon Connector
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	781786694392

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)