



# Locking Devices, Industrial, Flanged Inlet, 30A Phase Delta 600V AC, 3-Pole 3-Wire Non-Grounding, L13-30P, Screw Terminal, White

By Bryant  
Catalog # [71330MB](#)

Locking Devices, Industrial, Flanged Inlet, 30A Phase Delta 600V AC, 3-Pole 3-Wire Non-Grounding, L13-30P, Screw Terminal, White



## Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

## Application

Extra Heavy Duty Industrial

## Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	L13-30P

## Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	3-Pole

## Current

Dielectric Strength	Withstands 3500V
Current/Amperage Rating	30 Amp
Description	
Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	3 Phase 600V AC
Connectivity	Screw Terminals
Voltage Rating	3 Phase 600 VAC

## Dimensions

Display Size	Standard Sized Product
Length	2.88 in
Width	2.88 in
Height	2.02 in
Dimensions	2.88 in x 2.88 in x 2.02 in

## General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	White
Item Type	30A Flanged Inlet
Insulation	Insulated Body
Material - Mounting Hardware Type	Screw Mounting Flanged Inlet
Material	Composite
UPC	781786694767

## Logistics

Carton Quantity	10
-----------------	----

## Operational

Temperature Rating	<ul style="list-style-type: none"> <li>• Maximum Continuous: 75° C</li> <li>• Minimum Continuous: -40° C w/o impact</li> </ul>
--------------------	--

## Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)