

**Locking Devices, Industrial, Flanged Inlet, 20A 250V, 3-Pole 4-Wire Grounding, L14-20P, Screw Terminal, White, With Weatherproof Cover**

By Bryant  
 Catalog # [71420MBWP](#)



Locking Devices, Industrial, Flanged Inlet, 20A 250V, 3-Pole 4-Wire Grounding, L14-20P, Screw Terminal, White, With Weatherproof Cover

**Features**

- Flanged Inlet
- 20A 125/250V AC
- 3-Pole 4-Wire Grounding
- L14-20P
- Screw Terminal

**Application**

Extra Heavy Duty Industrial

**Specifications**

Environmental Conditions	Weather Resistant
EU RoHS Indicator	Yes
Nema Rating	L14-20P

**Conductor**

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	3-Pole

**Current**

Dielectric Strength	Withstands 3000V Minimum in
Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125/250 VAC
Connectivity	Screw Terminals
Voltage Rating	125/250 VAC

**Dimensions**

Display Size	Standard Sized Product
Length	2.88 in
Width	2.88 in
Height	2.02 in
Dimensions	2.88 in x 2.88 in x 2.02 in

**General**

OEM Brand Name	Hubbell Bryant
Style	Weatherprotective
Color	White
Item Type	20A Weather Protective Power Inlet
Insulation	Insulated Body
Material - Mounting Hardware	Screw Mounting
Type	Flanged Inlet
Material	Composite
UPC	781786695177

**Logistics**

Carton Quantity	10
-----------------	----

**Operational**

Temperature Rating	<ul style="list-style-type: none"> <li>• Maximum Continuous: 75° C</li> <li>• Minimum Continuous: -40° C w/o impact</li> </ul>
--------------------	--

**Product Assets**

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)