



Locking Devices, Industrial, Flanged Inlet,
30A 125/250V, 3-Pole 4-Wire Grounding,
L14-30P, Screw Terminal, White, With
Weatherproof Cover

By Bryant
Catalog # 71430MBWP

Locking Devices, Industrial, Flanged Inlet, 30A 125/250V, 3-Pole
4-Wire Grounding, L14-30P, Screw Terminal, White, With
Weatherproof Cover

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included
- Weather Protective Cover

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Weather Resistant
EU RoHS Indicator	Yes
Nema Rating	L14-30P

Conductor

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Dielectric Strength	Withstands 3500V
Current/Amperage Rating	30 Amp
Description	
Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	125/250 VAC
Connectivity	Screw Terminals
Voltage Rating	125/250 VAC



Dimensions

Display Size	Standard Sized Product
Length	2.88 in
Width	2.88 in
Height	2.02 in
Dimensions	2.88 in x 2.88 in x 2.02 in

General

OEM Brand Name	Hubbell Bryant
Style	Weatherprotective
Color	White
Item Type	30A Weather Protective Power Inlet
Insulation	Insulated Body
Material - Mounting Hardware	Screw Mounting
Type	Flanged Inlet
Material	Composite
UPC	781786695375

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)