



Locking Devices, Industrial, Flanged Inlet,  
20A 3-Phase Delta 250V AC, 3-Pole 4-Wire  
Grounding, L15-20P, Screw Terminal, With  
Weatherproof Cover

By Bryant  
Catalog # 71520MBWP

Locking Devices, Industrial, Flanged Inlet, 20A 3-Phase Delta  
250V AC, 3-Pole 4-Wire Grounding, L15-20P, Screw  
Terminal,White, With Weatherproof Cover

Features

- Flanged Inlet
- 20A 3-Phase Delta 250V AC
- 3-Pole 4-Wire Grounding
- L15-20P
- Screw Terminal

Application

Extra Heavy Duty Industrial

Specifications

|                          |                   |
|--------------------------|-------------------|
| Environmental Conditions | Weather Resistant |
| EU RoHS Indicator        | Yes               |
| Nema Rating              | L15-20P           |

Conductor

|                 |                   |
|-----------------|-------------------|
| Number Of Wires | 4-Wire            |
| Wire Size       | #18 AWG to #8 AWG |
| Number Of Poles | 3-Pole            |

Current

|                            |                             |
|----------------------------|-----------------------------|
| Dielectric Strength        | Withstands 3000V Minimum in |
| Current/Amperage Rating    | 20 Amp                      |
| Description                |                             |
| Current Rating             | 20 A                        |
| Amperage Rating            | 20 A                        |
| Voltage Rating Description | 3 Phase 250 VAC             |
| Connectivity               | Screw Terminals             |
| Voltage Rating             | 3 Phase 250 VAC             |



Dimensions

|              |                             |
|--------------|-----------------------------|
| Display Size | Standard Sized Product      |
| Length       | 2.88 in                     |
| Width        | 2.88 in                     |
| Height       | 2.02 in                     |
| Dimensions   | 2.88 in x 2.88 in x 2.02 in |

General

|                              |                                    |
|------------------------------|------------------------------------|
| OEM Brand Name               | Hubbell Bryant                     |
| Style                        | Weatherprotective                  |
| Color                        | White                              |
| Item Type                    | 20A Weather Protective Power Inlet |
| Insulation                   | Insulated Body                     |
| Material - Mounting Hardware | Screw Mounting                     |
| Type                         | Flanged Inlet                      |
| Material                     | Composite                          |
| UPC                          | 781786695870                       |

Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Operational

|                    |                                                                                                                             |
|--------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Temperature Rating | <ul style="list-style-type: none"><li>• Maximum Continuous: 75° C</li><li>• Minimum Continuous: -40° C w/o impact</li></ul> |
|--------------------|-----------------------------------------------------------------------------------------------------------------------------|

Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)