



## Locking Devices, Industrial, Flush Receptacle, 20A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, L16-20P, Screw Terminal, Black and White

By Bryant  
Catalog # [71620NP](#)

Locking Devices, Industrial, Flush Receptacle, 20A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, L16-20P, Screw Terminal, Black and White



### Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

### Application

Extra Heavy Duty Industrial

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance	CM
Status	
Nema Rating	L16-20P

### Conductor

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	3-Pole

### Configuration

Cord Type	All Listed Portables
-----------	----------------------

### Current

Current/Amperage Rating	20 Amp
Description	

Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	3 Phase 480 VAC
Phase	Three Phase
Connectivity	Screw Terminals
Voltage Rating	3 Phase 480 VAC

### Dimensions

Display Size	Standard Sized
Length	2.13 in
Width	2.13 in
Height	2.86 in
Dimensions	2.13 in x 2.13 in x 2.86 in

### General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Black, White
Item Type	20A Triple Gripper Nylon Plug
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786696921

### Logistics

Carton Quantity	10
Pallet Quantity	1680

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)