



## Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, L16-30R, Screw Terminal, Black

By Bryant  
Catalog # [71630FR](#)

Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, L16-30R, Screw Terminal, Black

### Features

- Combination back and side wiring terminals accept #14 through #8 AWG solid or stranded conductors
- Heavy duty mounting straps are nickel-plated to resist corrosion, wide width design assures secure assembly
- NEMA rating and configuration are molded into face for easy identification
- One-piece, rivetless copper-alloy contact design reduces heat buildup and provides secure blade retention

### Application

Extra Heavy Duty Industrial Specification Grade

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance	CM
Status	
Nema Rating	L16-30R

### Conductor

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	3-Pole

### Current

Current/Amperage Rating	30 Amp
Description	
Current Rating	30 A



Amperage Rating	30 A
Voltage Rating Description	3 Phase 480V AC
Phase	Three Phase
Connectivity	Terminal Screws
Voltage Rating	3 Phase 480 VAC

### Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.70 in
Height	1.24 in
Dimensions	3.28 in x 1.70 in x 1.24 in

### General

OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Item Type	30A Single Nylon Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786697133

### Logistics

Carton Quantity	10
Pallet Quantity	2340

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)