

Locking Devices, Industrial, Female Connector Body, 30A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, L16-30R, Screw Terminal, Black and White

By Bryant
Catalog # 71630NC



Locking Devices, Industrial, Female Connector Body, 30A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, L16-30R, Screw Terminal, Black and White

Features

-
-
-
-

Application

Heavy Duty Industrial

General

Catalog Number	71630NC
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Triple Gripper Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Style	Internal Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786697195

Dimensions

Dimensions	2.13 in x 2.13 in x 3.90 in
Display Size	Standard Sized Product

Height	3.9 in
Length	2.13 in
Width	2.13 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Voltage Rating	3 Phase 480 VAC
Voltage Rating Description	3 Phase 480 VAC

Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Wires	4-Wire
Number of Conductors	4-Wire Grounding
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L16-30R
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
Pallet Quantity	2000

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 71630NC Specification Sheet French](#)
[Specifications - 71630NC Specification Sheet English](#)