



Locking Devices, Industrial, Flanged
Receptacle, 30A 3-Phase Delta 600V AC,
3-Pole 4-Wire Grounding, L17-30R, Screw
Terminal, White

By Bryant
Catalog # 71730ER

Locking Devices, Industrial, Flanged Receptacle, 30A 3-Phase
Delta 600V AC, 3-Pole 4-Wire Grounding, L17-30R, Screw
Terminal, White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L17-30R

Conductor

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	30 Amp
Description	
Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	3 Phase 600V AC
Phase	Three Phase



Connectivity	Terminal Screws
Voltage Rating	3 Phase 600 VAC
Dimensions	
Display Size	Standard Sized Product
Length	2.88 in
Width	2.88 in
Height	2.02 in
Dimensions	2.88 in x 2.88 in x 2.02 in

General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	White
Item Type	30A Flanged Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Flanged Receptacle
Material	Composite
UPC	781786697607

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)