



Locking Devices, Industrial, Male Plug, 20A 3- PhaseWye 277/480V AC, 4-Pole 4-Wire Non-Grounding, L19-20P, Screw Terminal, Black and White

By Bryant
Catalog # 71920NP

Locking Devices, Industrial, Male Plug, 20A 3- PhaseWye 277/480V AC, 4-Pole 4-Wire Non-Grounding, L19-20P, Screw Terminal, Black and White

Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L19-20P

Conductor

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	4-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current

Current/Amperage Rating	20 Amp
Description	

Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	3 Phase Y 277/480 VAC
Phase	Three Phase
Connectivity	Screw Terminals
Voltage Rating	3 Phase Y 277/480 VAC

Dimensions

Display Size	Standard Sized
Length	2.13 in
Width	2.13 in
Height	2.86 in
Dimensions	2.13 in x 2.13 in x 2.86 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Black, White
Item Type	20A Triple Gripper Nylon Plug
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786699021

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)