



Locking Devices, Industrial, Flanged
Receptacle, 30A 3-Phase Wye 277/480V
AC, 4-Pole 4-Wire Non-Grounding, L19-
30R, Screw Terminal, White

By Bryant
Catalog # [71930ER](#)

Locking Devices, Industrial, Flanged Receptacle, 30A 3-Phase
Wye 277/480V AC, 4-Pole 4-Wire Non-Grounding, L19-30R,
Screw Terminal, White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L19-20R

Conductor

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	4-Pole

Current

Current/Amperage Rating	30 Amp
Description	
Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	3 Phase Y 277/480V AC



Phase	Three Phase
Connectivity	Terminal Screws
Voltage Rating	3 Phase Y 277/480 VAC

Dimensions

Display Size	Standard Sized Product
Length	2.88 in
Width	2.88 in
Height	2.02 in
Dimensions	2.88 in x 2.88 in x 2.02 in

General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	White
Item Type	30A Flanged Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Flanged Receptacle
Material	Composite
UPC	781786699403

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)