



Locking Devices, Industrial, Male Plug, 30A 3- Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, L21-30P, Screw Terminal, Black and White

By Bryant
Catalog # 72130NP



Locking Devices, Industrial, Male Plug, 30A 3- Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, L21-30P, Screw Terminal, Black and White

Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	L21-30P

Conductor

Number Of Wires	5-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	4-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current

Current/Amperage Rating Description	30 Amp
-------------------------------------	--------

Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	3 Phase Y 120/208 VAC
Phase	Three Phase
Connectivity	Screw Terminals
Voltage Rating	3 Phase Y 120/208 VAC

Dimensions

Display Size	Standard Sized
Length	2.13 in
Width	2.13 in
Height	2.86 in
Dimensions	2.13 in x 2.13 in x 2.86 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Black, White
Item Type	30A Triple Gripper Nylon Plug
Material - Mounting Hardware Type	Cord Mounted Plugs
Material	Composite
UPC	781786701526

Logistics

Carton Quantity	10
Pallet Quantity	2080

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)