



Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase Wye 277/480V AC, 4-Pole 5-Wire Grounding, L22-30R, Screw Terminal, Black

By Bryant
Catalog # [72230FR](#)



Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase Wye 277/480V AC, 4-Pole 5-Wire Grounding, L22-30R, Screw Terminal, Black

Features

- Combination back and side wiring terminals accept #14 through #8 AWG solid or stranded conductors
- Heavy duty mounting straps are nickel-plated to resist corrosion, wide width design assures secure assembly
- NEMA rating and configuration are molded into face for easy identification
- One-piece, rivetless copper-alloy contact design reduces heat buildup and provides secure blade retention

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance	CM
Status	
Nema Rating	L22-30R

Conductor

Number Of Wires	5-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	4-Pole

Current

Current/Amperage Rating	30 Amp
Description	
Current Rating	30 A

Amperage Rating	30 A
Voltage Rating Description	3 Phase Y 277/480V AC
Phase	Three Phase
Connectivity	Terminal Screws
Voltage Rating	3 Phase Y 277/480 VAC

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.70 in
Height	1.24 in
Dimensions	3.28 in x 1.70 in x 1.24 in

General

OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Item Type	30A Single Nylon Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786702134

Logistics

Carton Quantity	10
Pallet Quantity	2340

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)