



# Locking Devices, Industrial, Male Plug, 30A 3- Phase Wye 277/480V AC, 4-Pole 5-Wire Grounding, L22-30P, Screw Terminal, Black and White

By Bryant  
Catalog # 72230NP



## Features

- 
- 
- 
- 
- 
- 

## Application

Extra Heavy Duty Industrial

## General

Catalog Number	72230NP
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Triple Gripper Nylon Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
Style	Internal Cord Clamp
Type	Plugs
UPC	781786702226

## Dimensions

Dimensions	2.13 in x 2.13 in x 2.86 in
Display Size	Standard Sized
Height	2.86 in
Length	2.13 in

Width 2.13 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Phase	Three Phase
Voltage Rating	3 Phase Y 277/480 VAC
Voltage Rating Description	3 Phase Y 277/480 VAC

## Conductor Related

Cord Type	All Listed Portables
Number Of Wires	5-Wire
Wire Size	#18 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L22-30P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	2340

## Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 72230NP Specification Sheet French](#)
- [Specifications - 72230NP Specification Sheet English](#)