



Locking Devices, Industrial, Male Plug, 20A 3- Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L23-20P, Screw Terminal, Black and White

By Bryant
Catalog # 72320NP

Locking Devices, Industrial, Male Plug, 20A 3- Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L23-20P, Screw Terminal, Black and White

Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L23-20P

Conductor

Number Of Wires	5-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	4-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current

Amperage Rating	20 A
Voltage Rating Description	3 Phase Y 347/600 VAC



Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Voltage Rating	3 Phase Y 347/600 VAC
Connectivity	Screw Terminals
Phase	Three Phase

Dimensions

Length	2.13 in
Display Size	Standard Sized
Height	2.86 in
Width	2.13 in
Dimensions	2.13 in x 2.13 in x 2.86 in

General

Color	Black, White
Style	Internal Cord Clamp
OEM Brand Name	Hubbell Bryant
UPC	781786702721
Type	Plugs
Material - Mounting Hardware	Cord Mounted
Item Type	20A Triple Gripper Nylon Plug
Material	Composite

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)