



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 20A 3-Phase 120/208V AC, 4-Pole 4-Wire Non-Grounding, 18-20P

By Bryant
Catalog # 7251N

Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 20A 3-Phase 120/208V AC, 4-Pole 4-Wire Non-Grounding, 18-20P, Black, Single Pack

Features

- Heavy Duty
- Industrial/Commercial Grade
- Straight
- 20A 3-Phase 120/208V AC
- 4-Pole 4-Wire Non-Grounding

Application

Heavy Duty

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	18-20P

Conductor

Number Of Wires	4-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	4-Pole

Configuration

Cord Type	All Portable
-----------	--------------

Current

Current Rating	20 A
Amperage Rating	20 A



Voltage Rating Description	3 Phase WYE 120/208 VAC
Phase	Three Phase
Current / Amperage Rating	20 A
Connectivity	Screw Terminals
Wattage	4160
Voltage Rating	Three Phase Y 120/208 VAC

Dimensions

Display Size	Standard Sized
Weight	0.35 lb.

General

Series	Industrial
OEM Brand Name	Hubbell Bryant
Style	Heavy Duty
Color	Gray
Item Type	Standard
Material - Mounting Hardware	Cord Mounted
Type	Plug
Material	Composite
UPC	781786627932

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)