



Locking Devices, Industrial, Female
Connector Body, 20A 250V, 2-Pole 3-Wire
Grounding, Non-NEMA, Screw Terminal,
Yellow

By Bryant
Catalog # 7314NSY

Locking Devices, Industrial, Female Connector Body, 20A 250V,
2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Yellow

Features

- Female Nylon Connector Body
- 20A 250V
- 3-Pole 3-Wire Non-Grounding
- Non-NEMA
- Screw Terminal

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	Non-NEMA

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Conductors	4-Wire Non-Grounding
Conductor Range	#14 AWG to #12 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125/250 VAC
Connectivity	Screw Terminals

Voltage Rating	125/250 VAC
----------------	-------------

Dimensions

Display Size	Standard Sized Product
Length	2.11 in
Height	3.73 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Black, White
Item Type	20A Nylon Connector-For Replacement Use
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	781786667839

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)