



Locking Devices, Industrial, Flanged
Receptacle, 20A 250V, 2-Pole 3-Wire
Grounding, Non-NEMA, Screw Terminal,
Black

By Bryant
Catalog # 7328

Locking Devices, Industrial, Flanged Receptacle, 20A 250V, 2-
Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125/250V AC
Phase	Single Phase



Connectivity
Voltage Rating

Terminal Screws
125/250 VAC

Dimensions

Display Size	Standard Sized Product
Length	3.06 in
Width	3.06 in
Height	2.27 in
Dimensions	3.06 in x 3.06 in x 2.27 in

General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	Black
Item Type	20A Flanged Receptacle-For Replacement Use
Material - Mounting Hardware	Screw Mounting
Type	Flanged Receptacle
Material	Composite
UPC	781786628175

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)