



Locking Devices, Industrial, Receptacle, 50A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # 7379

Locking Devices, Industrial, Receptacle, 50A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black



Features

- 50A 250V DC/600V AC
- 3-Pole 4-Wire Grounding
- Non-NEMA
- Screw Terminal

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No

Conductor

Number Of Wires	4-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	50 Amp
Description	
Current Rating	50 A
Amperage Rating	50 A
Voltage Rating Description	250 VDC/600 VAC
Phase	Single Phase
Connectivity	Terminal Screws

Voltage Rating	250 VDC/600 VAC
----------------	-----------------

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	2.12 in
Height	2.44 in
Dimensions	3.28 in x 2.12 in x 2.44 in

General

OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Color	Black
Item Type	50A Single Armored Heavy Duty Receptacle-For Replacement Use
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786668508

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)