



Locking Devices, Industrial, Flush
Receptacle, 20A 3-Phase Wye 120/208V
AC, 4-Pole 4-Wire Non-Grounding, Non-
NEMA, Screw Terminal, Black

By Bryant
Catalog # [7410](#)

Locking Devices, Industrial, Flush Receptacle, 20A 3-Phase Wye
120/208V AC, 4-Pole 4-Wire Non-Grounding, Non-NEMA, Screw
Terminal, Black

Features

- Flush Receptacle
- 20A 3-Phase Wye 120/208V AC
- 4-Pole 4-Wire Non-Grounding
- Non-NEMA
- Screw Terminal

Application

Extra Heavy Duty Industrial Specification Grade

Specifications


Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	Non-NEMA

Conductor

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	4-Pole

Current

Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	3 Phase Y 120/208V AC



Phase	Three Phase
Connectivity	Terminal Screws
Voltage Rating	3 Phase Y 120/208 VAC

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.71 in
Height	1.14 in
Dimensions	3.28 in x 1.71 in x 1.14 in

General

OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Item Type	20A Single Receptacle-For Replacement Use
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786628311

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)