



Locking Devices, Industrial, Female Connector Body, 20A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non-Grounding, Non- NEMA, ScrewTerminal

By Bryant
Catalog # 7414

Locking Devices, Industrial, Female Connector Body, 20A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non-Grounding, Non-NEMA,ScrewTerminal, Black and White

Features

- Female Nylon Connector Body
- 20A 3-Phase Wye 120/208V AC
- 4-Pole 4-Wire Non-Grounding
- Non-NEMA
- Screw Terminal

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Conductors	4-Wire Non-Grounding
Conductor Range	#14 AWG to #12 AWG
Number Of Poles	4-Pole

Current

Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	3 Phase Y 120/208 VAC
Connectivity	Screw Terminals

Voltage Rating	3 Phase Y 120/208 VAC
----------------	-----------------------

Dimensions

Display Size	Standard Sized Product
Length	2.11 in
Height	3.73 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Sentinel Yellow
Item Type	20A Nylon Connector-For Replacement Use
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	781786628380

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	- Maximum Continuous: 75° C - Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)