



Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125V, 2-Pole 2-Wire Non-Grounding, ML-1R, Screw Terminal, Black & White

By Bryant
Catalog # 7464N

Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125V, 2-Pole 2-Wire Non-Grounding, ML-1R, Screw Terminal, Black & White

Features

- Smaller body size for use in tighter fit applications where larger products can't
- Abuse resistant nylon housing

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	ML-1R

Conductor

Number Of Conductors	2-Pole Non-Grounding
Number Of Wires	2-Wire
Wire Size	#18 AWG to #12 AWG
Number Of Poles	2-Pole
Conductor Range	#14 AWG

Current

Amperage Rating	15 A
Voltage Rating Description	125 V
Current/Amperage Rating Description	15 Amp
Current Rating	15 A
Voltage Rating	125 V
Connectivity	Screw Terminals



Dimensions

Length	1.25 in
Display Size	Midget NEMA Locking
Height	2.15 in
Width	1.25 in
Dimensions	1.25 in x 1.25 in x 2.15 in

General

Style	Non-Grounding
OEM Brand Name	Hubbell Bryant
UPC	781786638501
Type	Plugs
Material - Mounting Hardware	Cord Mounted
Insulation	Insulated Body
Item Type	15A Midget Female Connector
Material	Composite

Logistics

Pallet Quantity	16500
Carton Quantity	10

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)