



Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125V, 2-Pole 2-Wire Non-Grounding, ML-1R, Screw Terminal, Black

By Bryant
Catalog # 7464NB

Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125V, 2-Pole 2-Wire Non-Grounding, ML-1R, Screw Terminal, Black

Features

- Smaller body size for use in tighter fit applications where larger products can't
- Abuse resistant nylon housing

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	ML-1R

Conductor

Number Of Wires	2-Wire
Wire Size	#18 AWG to #12 AWG
Number Of Conductors	2-Pole Non-Grounding
Conductor Range	#14 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating	15 Amp
Description	
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Connectivity	Screw Terminals
Voltage Rating	125 V



Dimensions

Display Size	Midget NEMA Locking
Length	1.25 in
Width	1.25 in
Height	2.15 in
Dimensions	1.25 in x 1.25 in x 2.15 in

General

OEM Brand Name	Hubbell Bryant
Style	Non-Grounding
Item Type	15A Midget Female Connector
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786616608

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)