



Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125/250V, 3-Pole 3-Wire Non Grounding, ML-3R, Screw Terminal & White

By Bryant
Catalog # 7484NC

Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125/250V, 3-Pole 3-Wire Non Grounding, ML-3R, Screw Terminal, Black & White

Features

- Smaller body size for use in tighter fit applications where larger products can't
- Abuse resistant nylon housing

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	ML-3R

Conductor

Number Of Conductors	3-Wire Non-Grounding
Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG
Number Of Poles	3-Pole
Conductor Range	#14 AWG

Current

Amperage Rating	15 A
Voltage Rating Description	125/250 V
Current/Amperage Rating	15 Amp
Description	
Current Rating	15 A
Voltage Rating	125/250 V
Connectivity	Screw Terminals

Dimensions

Length	1.25 in
Display Size	Midget NEMA Locking
Height	2.15 in
Width	1.25 in
Dimensions	1.25 in x 1.25 in x 2.15 in

General

Style	Non-Grounding
OEM Brand Name	Hubbell Bryant
UPC	781786669352
Type	Connector Body
Material - Mounting Hardware	Cord Mounted
Insulation	Insulated Body
Item Type	15A Midget Female Connector
Material	Composite

Logistics

Pallet Quantity	5850
Carton Quantity	10

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)