



Locking Devices, Bryant Midget Locking, Industrial, Flanged Inlet, 15A 125/250V, 3-Pole 3-Wire Non Grounding, ML-3P, Screw Terminal, Black & White

By Bryant
Catalog # 7486MB

Locking Devices, Bryant Midget Locking, Industrial, Flanged Inlet, 15A 125/250V, 3-Pole 3-Wire Non Grounding, ML-3P, Screw Terminal, Black & White

Features

- Industrial
- Flanged Inlet
- 15A 125/250V
- 3-Pole 3-Wire Non Grounding
- ML-3P

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	ML-3P

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG
Number Of Poles	3-Pole

Current

Dielectric Strength	Withstands 3000V Minimum in
Current/Amperage Rating	15 Amp
Description	
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125/250V
Connectivity	Screw Terminals
Voltage Rating	125/250 V



Dimensions

Display Size	Midget Locking
Length	2.06 in
Width	1.62 in
Height	1.17 in
Dimensions	2.06 in x 1.62 in x 1.17 in

General

OEM Brand Name	Hubbell Bryant
Style	Non-Grounding
Color	White
Item Type	15A Midget Flanged Inlet
Insulation	Insulated Body
Material - Mounting Hardware	Screw Mounting
Type	Flanged Inlet
Material	Composite
UPC	781786669451

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)