



Locking Devices, Locking Devices,
Industrial, Female Connector Body, 15A
125V, 2-Pole 2-Wire Non Grounding, L1-15R,
Screw Terminal, Black and White

By Bryant
Catalog # 7506

Locking Devices, Locking Devices, Industrial, Female Connector
Body, 15A 125V, 2-Pole 2-Wire Non Grounding, L1-15R, Screw
Terminal, Black and White

Features

- Female Connector Body
- 15A 125V
- 2-Pole 2-Wire Non Grounding
- L1-15R
- Screw Terminal

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	L1-15R

Conductor

Number Of Wires	2-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Conductors	2-Pole Non-Grounding
Conductor Range	#14 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating	15 Amp
Description	
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Connectivity	Screw Terminals
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Length	1.53 in
Width	1.53 in
Height	2.78 in
Dimensions	1.53 in x 1.53 in x 2.78 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Black, White
Item Type	15A Nylon Connector
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	781786628939

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)