



Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 50A 125/250V, 3-Pole 3-Wire Non Grounding, 10-50R

By Bryant
Catalog # 7516NC

Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 50A 125/250V, 3-Pole 3-Wire Non Grounding, 10-50R, Gray, Single Pack



Features

- Heavy Duty
- Industrial/Commercial Grade
- Straight
- 50A 125/250V
- 3-Pole 3-Wire Non Grounding

Application

Heavy Duty

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	10-50R

Conductor

Number Of Wires	3-Wire
Number Of Conductors	3-Wire Non-Grounding
Conductor Range	#6 AWG
Number Of Poles	3-Pole

Current

Current Rating	50 A
Amperage Rating	50 A
Voltage Rating Description	125/250 V
Current / Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Voltage Rating	125/250 V

Dimensions

Display Size	Standard Sized Product
Length	2.59 in
Width	5.19 in
Weight	1.15 lb.
Height	3.12 in
Dimensions	2.59 in x 5.19 in x 3.12 in

General

Series	Industrial
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Color	Black
Item Type	Standard
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	781786732438

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)