



Locking Devices, Industrial, Receptacle, 15A 125V, 2-Pole 2-Wire Non-Grounding, L1-15R, Screw Terminal, Black

By Bryant
Catalog # 7535



Locking Devices, Industrial, Receptacle, 15A 125V, 2-Pole 2-Wire Non-Grounding, L1-15R, Screw Terminal, Black

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	7535
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Single Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Style	Single Receptacle
Type	Receptacle
UPC	781786629165

Dimensions

Display Size	Standard Sized Product
Height	1 in

Length 3.28 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125V

Conductor Related

Number Of Wires	2-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L1-15R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 7535 Specification Sheet English](#)
[Specifications - 7535 Specification Sheet French](#)