



Locking Devices, Industrial, Flanged
Receptacle, 15A 125V/10A 250V, 3-Pole 3-
Wire Non Grounding, Non-NEMA, Screw
Terminal, Black

By Bryant
Catalog # 7557ER

Locking Devices, Industrial, Flanged Receptacle, 15A 125V/10A
250V, 3-Pole 3-Wire Non Grounding, Non-NEMA, Screw Terminal,
Black

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	10 Amp
Description	
Current Rating	10 A
Amperage Rating	10 A
Voltage Rating Description	250V
Phase	Single Phase



Connectivity	Terminal Screws
Voltage Rating	250 V

Dimensions

Display Size	Standard Sized Product
Length	1.84 in
Width	2.38 in
Height	1.68 in
Dimensions	1.84 in x 2.38 in x 1.68 in

General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	White
Item Type	10A Triple Gripper Flanged Receptacle Non-NEMA
Material - Mounting Hardware	Screw Mounting
Type	Flanged Receptacle
Material	Composite
UPC	781786405851

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)