



Locking Devices, Marine Grade, Female Connector Body, 15A 125V/10A 250V, 3-Pole 3-Wire Non Grounding, Non-NEMA, Screw Terminal, Yellow

By Bryant
Catalog # 7565NCCR

Locking Devices, Marine Grade, Female Connector Body, 15A 125V/10A 250V, 3-Pole 3-Wire Non Grounding, Non-NEMA, Screw Terminal, Yellow

Features

- Female Connector Body
- 10A 250V
- 3-Pole 3-Wire Non Grounding
- Non-NEMA
- Screw Terminal

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	Non-NEMA

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Conductors	3-Wire Non-Grounding
Conductor Range	#14 AWG to #12 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	10 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	250 V
Connectivity	Screw Terminals
Voltage Rating	250 V



Dimensions

Display Size	Standard Sized Product
Length	1.53 in
Width	1.53 in
Height	2.95 in
Dimensions	1.53 in x 1.53 in x 2.95 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Black, White
Item Type	10A Triple Gripper Nylon Connector Non-NEMA
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	781786010604

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)