



Locking Devices, Industrial, Male Plug, 15A 125V/10A 250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # 7568NP

Locking Devices, Industrial, Male Plug, 15A 125V/10A 250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black

Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	3-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current

Current/Amperage Rating	10 Amp
Description	



Current Rating	10 A
Amperage Rating	10 A
Voltage Rating Description	250 V
Phase	Single Phase
Connectivity	Screw Terminals
Voltage Rating	250 V

Dimensions

Display Size	Standard Sized
Length	1.53 in
Width	1.53 in
Height	2.18 in
Dimensions	1.53 in x 1.53 in x 2.18 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Black, White
Item Type	10A Triple Gripper Nylon Plug Non-NEMA
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786010451

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)