



Locking Devices, Industrial, Duplex
Receptacle, 15A 125V/10A 250V, 3-Pole 3-
Wire Non-Grounding, Non-NEMA, Screw
Terminal, Black

By Bryant
Catalog # 7580DR

Locking Devices, Industrial, Duplex Receptacle, 15A 125V/10A
250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal,
Black

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- Single point break-off tabs
- Mounting strap tabs lock the body and base together

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	Non-NEMA

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	10 Amp
Description	
Current Rating	10 A
Amperage Rating	10 A
Voltage Rating Description	250V



Phase	Single Phase
Connectivity	Terminal Screws
Voltage Rating	250 V

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.38 in
Height	1.41 in
Dimensions	3.28 in x 1.38 in x 1.41 in

General

OEM Brand Name	Hubbell Bryant
Style	Duplex Receptacle
Item Type	10A Duplex Receptacle Non-NEMA
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786002142

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)